


surface nickel plated [ⓑ]


Oberfläche
vernickelt 3-6 µm



[ⓑ] rings bump positions as accurately as possible aligned

[ⓑ] spot welded

[ⓑ]

Tolerierung: DIN 7167 Allgemeintoleranzen: measure of linear and general Tolerances angular dimensions and tolerances for features			Längenmaße: Winkel, Form u. Lage: DIN ISO 2768-mK-E			material: steel wire (b) Werkstoff: Stahldraht Ø1.5 DIN EN 10218-2			(a)		
AutoCAD						Artikel Schutzgitter LZ22N guard grille (b)			Maßstab 1:1		
	Datum	Name									
Bearbeitet	10.12.2002	SEIDLER	 PAPST-MOTOREN GmbH & Co KG D-78112 St. Georgen Germany			Zchg.-Nr. 9920022001			Blatt 001		
	B	000000103562									
	Index	Aend.-Nr.									
Geprüft u. zur Verwendung freigegeben von SEIDLER am 10.12.2002						Ers.f.Zchg.: GL. NR. V. 17.10.79			A4		