



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER E.O. P15649	16JUN1998	JW	RDR
	B	REVISED PER E.O P16308	04OCT1999	DS	DM
	C	REVISED PER PCN E-18-001206	24JAN2018	JA	DM
	C1	REVISED PER PCN E-19-018080	19NOV2019	MK	DM



TE INTERNAL PN	DEUTSCH PN	PLATING
0462-209-16141	0462-209-16141	NICKEL
0462-209-1631	0462-209-1631	GOLD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02OCT1999 D. SPENCER		
DIMENSIONS: INCHES [mm]		CHK 04OCT1999 M. GONZALES		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 04OCT1999 R. REED	NAME CONTACT SOCKET SIZE 16	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-151004	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL		APPLICATION SPEC 114-151004	A3 4AFU8 C=0462-209-16XX -	
FINISH		WEIGHT 0.60g	SCALE 10:1 SHEET 1 OF 1 REV C1	
		CUSTOMER DRAWING		

(C1) 1. SEE APPLICATION SPECIFICATION 114-151004 FOR CRIMP TOOLS AND WIRE RANGE.

NOTES: