

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1054051206

Status:

Active

Overview:

Nano-Fit Power Connectors

Description:

Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Dual Row, 6 Circuits, 0.38µm Gold (Au) Plating, Black, Glow-Wire Capable

Documents:

- Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification 1054051000-PS-CH-000 (PDF)

Product Specification 1054051000-PS-ES-000 (PDF)

Product Specification 1054051000-PS-SK-000 (PDF)

Product Specification PS-105405-001-001 (PDF)
- Application Specification AS-105405-001-001 (PDF)

Packaging Specification PK-105405-002-000 (PDF)

Test Summary 1054050000-TS-000 (PDF)

Datasheet (PDF)

Symbol Footprint Data SYM-105405-XX06-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

105405

Power, Wire-to-Board

Nano-Fit Power Connectors

Nano-Fit

889056258111

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Temperature Range - Operating

Termination Interface: Style

No

6

6

Black

50

Yes

Yes

Yes

Brass

Gold

Tin

Liquid Crystal Polymer

0.940/g

2

Right Angle

No

Yes

1.60mm

Embossed Tape on Reel

2.50mm

2.50mm

0.381µm

0.762µm

Yes

Yes

Yes

-40° to +115°C

Surface Mount

Electrical

Current - Maximum per Contact

Voltage - Maximum

7.0A

250V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

105405 Series

Mates With

Nano-Fit Receptacle Housing [1053081206](#) .
Nano-Fit Cable Assembly [45130](#)

Material Info

Reference - Drawing Numbers

Application Specification	AS-105405-001-001
Packaging Specification	PK-105405-002-000
Product Specification	1054051000-PS-CH-000, 1054051000-PS-ES-000, 1054051000-PS-SK-000, PS-105405-001-001
Sales Drawing	SD-105405-001-000
Symbol/Footprint Data	SYM-105405-XX06-001
Test Summary	1054050000-TS-000

This document was generated on 09/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION