




COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUBICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



RoHS compliant
by exemption

Packing unit on supplement AM0665
max. torque are 40 Ncm
Part-No. 4, 5, 9, 10 and 11 not mounted
Part-No. 6 alternatively in Zinc die-cast, tin plated



11	1	High power contact	FMP006S103	20A / AWG 12-16
10	1	High power contact	FMP006P103	20A / AWG 12-16
9	1	Rubber bushing	TPE	black
8	2	Locking screw	FVS1/5-K1163 M3 / Steel	nickel plated
7	2	Locking screw	FVS1/5-K1163 4-40 / Steel	nickel plated
6	1	Strain relief	ABS	nickel plated
5	1	Cable clamp	Steel	tin plated
4	4	Screw	Case hardened steel	zinc plated
3	2	Catch spring	PEI	black
2	1	Hood	FMK1G / Zinc die-cast	nickel plated
1	1	Mixed-Layout Connector	F2W2PC-K120	
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					molex		
SYMBOLS		DIMENSION UNITS	SCALE	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m	FCT Hood Connector Set		
= 0		mm	2:1				
= 0				CURRENT REVISION	PRODUCT CUSTOMER DRAWING		
= 0				DRWN: DRAWN BY ameyerrichte 10-08-2021			
= 0				APPR: APPR BY BWittek 12-08-2021			
= 0				INITIAL REVISION	MATERIAL NUMBER		
= 0				DRWN: DRAWN BY ameyerrichte 10-08-2021			
= 0				APPR: APPR BY BWittek 12-08-2021			
= 0		REV.	CH.-NO.		1731140981		
= 0		REPLACEMENT FOR:	THIRD ANGLE PROJECTION	DRAWING	DOCUMENT NUMBER		
= 0				A3-SIZE	FMK1G-2W2PC-6194		
					CUSTOMER		REVISION
					GENERAL MARKET		1
					SHEET NUMBER		1 OF 1