









reverse side
1 : 1

RoHS compliant
by exemption

Packing unit on supplement AM0665

max. torque are 40 Ncm
Part-No. 4, 5, 10 and 11 not mounted



11	5	High power contact	FMP006S103	20A / AWG 12-16
10	1	Rubber bushing	TPE	black
9	2	Locking screw	FVS1/5-K1163 M3 / Steel	nickel plated
8	2	Locking screw	FVS1/5-K1163 4-40 / Steel	nickel plated
7	2	Cable reduction plate	Zinc die-cast	nickel plated
6	1	Strain relief	ABS	nickel plated
5	1	Cable clamp	Steel	tin plated
4	4	Screw	Case hardened steel	zinc plated
3	2	Catch spring	PEI	black
2	1	Hood	FMK3G / Zinc die-cast	nickel plated
1	1	Mixed-Layout Connector	FM5W5S-K121	
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
 = 0		DIMENSION UNITS mm		SCALE 2:1		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m			molex									
 = 0						CURRENT REVISION							FCT Hood Connector Set					
 = 0																		
 = 0						DRWN: DRAWN BY ameyerrichte 10-08-2021 APPR: APPR BY BWittek 12-08-2021			PRODUCT CUSTOMER DRAWING									
 = 0																		
 = 0						INITIAL REVISION											MATERIAL NUMBER	
 = 0		1																
 = 0		REV.		CH.-NO.		DRWN: DRAWN BY ameyerrichte 10-08-2021 APPR: APPR BY BWittek 12-08-2021							1731140990				1	
 = 0		REPLACEMENT FOR:			THIRD ANGLE PROJECTION		DRAWING			DOCUMENT NUMBER				CUSTOMER		SHEET NUMBER		
= 0							A3-SIZE			FMK3G-5W5S-6198				GENERAL MARKET		1 OF 1		

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.