



COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



RoHS compliant
by exemption

Packing unit on supplement AM0665

max. torque are 40 Ncm
Part-No. 4, 5, 10, 11 and 12 not mounted



øF1 = Cable diameter without rubber bushing ø3 - ø8.5mm
øF2 = Cable diameter with rubber bushing max. ø6.5mm

12	2	High power contact	FMP003S103	20A / AWG 12-14
11	5	Crimp contact	FK20SL-02V	0.2µm Au / AWG 20-24
10	1	Rubber bushing	TPE	black
9	2	Locking screw	FVS1/5-K1163 M3 / Steel	nickel plated
8	2	Locking screw	FVS1/5-K1163 4-40 / Steel	nickel plated
7	2	Cable reduction plate	Zinc die-cast	nickel plated
6	1	Strain relief	ABS	nickel plated
5	1	Cable clamp	Steel	tin plated
4	4	Screw	Case hardened steel	zinc plated
3	2	Catch spring	PEI	black
2	1	Hood	FMK2G / Zinc die-cast	nickel plated
1	1	Mixed-Layout Connector	FL7W2S7-K121	
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m
	mm	2:1	
			CURRENT REVISION
			DRWN: DRAWN BY ameyerrichte 28-09-2021
			APPR: APPR BY BWittek 06-10-2021
			INITIAL REVISION
			DRWN: DRAWN BY ameyerrichte 28-09-2021
			APPR: APPR BY BWittek 06-10-2021
	REV.	CH.-NO.	
	REPLACEMENT FOR:	THIRD ANGLE PROJECTION	DRAWING
			A3-SIZE
		DOCUMENT NUMBER	CUSTOMER
		FMK2G-7W2S7-6199	GENERAL MARKET
		MATERIAL NUMBER	REVISION
		1731140992	1
		SHEET NUMBER	1 OF 1