



DESCRIPTION	QTY	MATERIAL	FINISH / COLOUR
COVER	1	PA9T V0 (E90350)	BLACK
HOUSING	1		BLACK
CENTRE PIN	1	BRASS	NICKEL PLATED
CONTACT 1	1	BRASS	TIN PLATED
CONTACT 2	1	BRASS	TIN PLATED
CONTACT 3	1	PHOSPHOR BRONZE	TIN PLATED



ISS.	AMEND	DATE
1	ISSUED	01/12/15
2	PA9T WAS LCP	20/03/19




FRONT FACE






SCHEMATIC

FRONT FACE



PCB LAYOUT  
BOTTOM VIEW



LOGO FONT  
BOOKMAN OLD STYLE

**NOTES:-**

- SUITABLE FOR USE WITH  $\varnothing 2.1\text{mm}$  OR  $\varnothing 2.5\text{mm}$  DC PLUG.
- RATED: 2A / 12V DC.  
 INSERTION / WITHDRAWAL FORCE: 0.3-2 kgf.  
 LIFE: 5,000 INSERTIONS MINIMUM.  
 CONTACT RESISTANCE:  
 INITIAL: PLUG / CONTACT <math>< 50\text{m}\Omega</math>, CONTACT / SHUNT <math>< 30\text{m}\Omega</math>.  
 AFTER LIFE TEST: PLUG / CONTACT <math>< 100\text{m}\Omega</math>, CONTACT / SHUNT <math>< 60\text{m}\Omega</math>.

PART No.	DESCRIPTION	SUPPLIED
FC681465S	SMD DC10LS	BAGGED / LOOSE
FC681465ST	SMDT DC10LS	TAPED 250x PER REEL

**RoHS**  
COMPLIANT

**TOLERANCE**  
 NO DEC. PLACE  $\pm 0.50$   
 1 DEC. PLACE  $\pm 0.30$   
 2 DEC. PLACE  $\pm 0.15$   
 HOLE  $\varnothing \pm 0.10$   
 ANGLES  $\pm 2^\circ$   
 UNLESS  
 OTHERWISE STATED

DO NOT SCALE

**Cliff Electronic Components Ltd.**

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,  
 Redhill, Surrey, RH1 2PF, England, UK  
 Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED  
 TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2015

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: SEE TABLE

FINISH: CLEAN

DRAWN: NJB

APPROVED: DPJ

TITLE: SMD DC10LS DUAL SOCKET

DRWG. No. **FC681465S**

FORM: A4DRWGH