









注)
NOTES

1. 材質

MATERIAL
ハウジング：ガラス入りPPS、茶色、UL94V-0
HOUSING:G.F.PPS,BROWN,UL94V-0
ターミナル：銅合金（t=0.2）
TERMINAL:COPPER ALLOY
吸着カバー：ステンレス（t=0.2）
VACUUM COVER:STAINLESS STEEL

2. メッキ仕様 PLATING

接点部 : 金メッキ 0.25 μ mMIN.
CONTACT AREA : GOLD 0.25 MICROMETER MIN.
半田付け部 : 錫メッキ 1.0 μ mMIN.
SOLDER TAIL AREA : TIN 1.0 MICROMETER MIN.
下地メッキ : ニッケルメッキ 1.5 μ mMIN.
UNDER-PLATING : NICKEL 1.5 MICROMETER MIN.

3. テールのバラツキ寸法

テール平坦度は、0.1 MAX.とする。
TAILS COPLANARITY TO BE 0.1MAX.


4. 本製品は 53647-***2 の鉛フリー品である。

THIS PRODUCT IS LEAD FREE OF 53647-***2.

無し WITHOUT	53.77	52.67	50.165	57.67	53647-1674	160
	47.42	46.32	43.815	51.32	53647-1474	140
	41.07	39.97	37.465	44.97	53647-1274	120
	34.72	33.62	31.115	38.62	53647-1074	100
	28.37	27.27	24.765	32.27	53647-0874	80
有り WITH	22.02	20.92	18.415	25.92	53647-0674	60
	15.67	14.57	12.065	19.57	53647-0474	40
	12.5	11.4	8.89	16.4	53647-0374	30
	9.32	8.22	5.715	13.22	53647-0274	20
ハウジングロック HSG LOCK	D	C	B	A	エンボス梱包 EMBOSSED PACKAGE ----- オーダー番号 ORDER NO.	極数 CKT

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex				
10 UNDER	± 0.2	mm- GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 612735		0.635 PITCH B-TO-B PLUG HS'G COVER ASS'Y -LEAD FREE-				
10 OVER 30 UNDER	± 0.25			DRWN: GSHARMA2019/02/26						
30 OVER	± 0.3			CHK'D: MSASAO2019/02/26						
ANGULAR $\pm 3^\circ$				APPR: MSASAO2019/02/26						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				INITIAL REVISION:		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
				DRWN: YWADA2004/03/23		SD-53647-002		PSD	001	H1
		APPR: MSASAO2004/03/24								
		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER	SHEET NUMBER	
				A3-SIZE	53647	SEE CHART		GENERAL MARKET	1 OF 2	

DOCUMENT STATUS	P1	RELEASE DATE	2019/02/26	07:19:48
-----------------	----	--------------	------------	----------



嵌合高さ一覧 Stacking Height variation			
	6	52885 series	55091 series
	7		53625 series
○	8		53647 series
	9		53649 series
	10		53627 series
	12	52901 series	55091 series
	13		53625 series
○	14		53647 series
	15		53649 series
	16		53627 series
本図製品該当高さ Height Application	嵌合高さ E Stacking Height	リセプタクル Receptacle	プラグ Plug

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
10 UNDER ± 0.2		mm		-		EC NO: 612735 DRWN: GSHARMA 2019/02/26 CHK'D: MSASAO 2019/02/26 APPR: MSASAO 2019/02/26 INITIAL REVISION: DRWN: YWADA 2004/03/23 APPR: MSASAO 2004/03/24								0.635 PITCH B-TO-B PLUG HS'G COVER ASS'Y -LEAD FREE-	
10 OVER 30 UNDER ± 0.25		GENERAL TOLERANCES (UNLESS SPECIFIED)													
30 OVER ± 0.3		ANGULAR TOL ± 3.0°													
ANGULAR ± 3°		4 PLACES ± 0.2													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		3 PLACES ± 0.25													
		2 PLACES ± 0.3													
		1 PLACE ±													
		0 PLACES ±													
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		53647		SEE CHART		GENERAL MARKET		2 OF 2	
										DOCUMENT NUMBER		DOC TYPE		DOC PART	
										SD-53647-002		PSD		001	
														H1	

