



**Notes:**

1. Material and Finish:
  - Coupler Ring: Zinc Die-Cast, Nickel Plated
  - Plug Housing: Zinc Die-Cast, Nickel Plated
  - Cable Gland: Brass, Nickel Plated
  - Cable Gland Rubber Ring: NBR, Color: Black
  - Cable Fitting: PA (Black), UL94 V-0
  - Interfacial Seal: Silicone, Color: White
  - Protective Cap: Polyester (Black); UL94 V-0
  - Tether: Polycarbonate (Black)

**Duplex LC Connector**

- Housing: PEI, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green**
- Inner Sub Assembly: Zirconia, Metal and PTFE
- Crimp Barrel: Brass, Nickel Plated
- Ferrule: Brass, Nickel Plated
- Dust Cap: PC, Color: White
- Duplex LC Clip: PC, Color: Black
- Operating Temperature: -40°C to +85°C

2. IP67 rated when covered or fully mated with the appropriate mating connector
3. Accepts 4.5mm to 8.0mm outside diameter fiber optic cable

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Nickel Plated Die-Cast Duplex LC Single Mode Plug Kit + Plastic Plug Cover Assembly	17-300410
Nickel Plated Die-Cast Duplex LC Multi Mode Plug Kit + Plastic Plug Cover Assembly	17-300420
Nickel Plated Die-Cast Duplex LC APC Single Mode Plug Kit + Plastic Plug Cover Assembly	17-300430

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Scale:	Dim. in mm
	Name	Title	Approval Date			Material: See Notes	
						Title: IP67 Industrial Duplex LC Plug + Protective Cover Assembly Kit	
						Nickel Plated Zinc Die-Cast Version	
						Drawing No.: 17K1A303	
			Part No.: SEE PART NUMBER TABLE		DIN A3		
					Sheet 1/1		

