



DC2.1\*5.5 DC SOCKET  
Black PVC/Nickel




DC2.1\*5.5 DC PLUG  
Black PVC/Nickel

CABLE CONSTRUCTION



WIRING DIAGRAM



**Specifications:**

Withstand Voltage : 300V / min.

Insulation Resistance : 10MΩ / min.

Conductor Resistance : 200Ω / KM Test

Temperature : 20°C

Current Rating : 1.2A

Connector Type A : 2.1mm DC Power Socket

Connector Type B : 2.1mm DC Power Plug Jacket

Colour : Black

Cable Assembly Type : Power

Mark	Qty	Change content	signatory	Date	Product name	LEAD R.A PLUG TO SKT 2.10MM DC, BLK	material	colour	unit	view
									mm	
		Design	technology		Model					
		Check	standardization		Drawing No					
		Approve	Date	2022.03.01						