



| REVISIONS |                           |      |       |
|-----------|---------------------------|------|-------|
| REV       | DESCRIPTION, EGN, EAR NO. | DATE | APP'D |
| A         | DRAWING PER EAR XXXX      | TBD  | TBD   |



Product Specification

Material

Insulator : Glass-Filled Thermoplastic PBT,UL94V-0  
 Contact : Copper alloy  
 Front shell : Steel, 60u" Nickel Over 50u" min Copper  
 Back shell : Steel, 100u" Tin Over 50u" min Copper

Electrical

Contact Resistance : 20 milliohms  
 Insulation Resistance : 1000 magohms at 500 VDC  
 Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute  
 Current Rating : 3 AMP  
 Volatge Rating : 250 VAC/rms 60Hz




Dimensions

| Positions | A     | B     | C     | E     | F     |
|-----------|-------|-------|-------|-------|-------|
| 9         | 30.81 | 24.99 | 16.92 | 11.08 | 19.20 |
| 15        | 39.20 | 33.30 | 25.25 | 19.39 | 27.70 |
| 25        | 53.05 | 47.04 | 38.96 | 33.24 | 41.10 |
| 37        | 69.40 | 63.50 | 55.42 | 49.86 | 57.30 |

ORDERING CODE: NFD17-AXXPB-2E1B-A

NUMBER OF CONTACTS:

- 09: 09 POSITION
- 15: 15 POSITION
- 25: 25 POSITION
- 37: 37 POSITION



50 Positions



|                            |                        |                      |
|----------------------------|------------------------|----------------------|
| UNLESS SPECIFIED OTHERWISE | DRAWN ED.LIU           | JUL22/22             |
| PRIMARY UNITS MILLIMETERS  | CHECKED TBD            | TBD                  |
| SECONDARY                  | M.E. APP'D             |                      |
| REFERENCE IN PARENTHESES   | Q.A. APP'D             |                      |
| GENERAL TOLERANCES         | DWG APP'D TBD          | TBD                  |
| 1 DECIMAL PLACE ±0.38      | ENG. REL. NO. EAR XXXX |                      |
| 2 DECIMAL PLACES ±0.25     | REF.                   |                      |
| 3 DECIMAL PLACES           | THIRD ANGLE PROJECTION | DO NOT SCALE DRAWING |
| ANGULAR DEGREES ±2°        |                        |                      |

Amphenol Canada Corp.  
Commercial Products

NFD17 SERIES MALE  
D-SUB CONNECTOR,  
RoHS COMPLIANT

|                      |              |
|----------------------|--------------|
| DWG NO.              | REV          |
| P-NFD17-AXXPB-2E1B-A | A            |
| CODE ID NO. 03554    | DWG SIZE X   |
| SCALE XX:1           | SHEET 1 OF 1 |