







P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	14FEB2022	PS	SB



SECTION A-A



SECTION B-B




CBS95-2P...

UL 1059
CSA C22.2 No. 158-10
1000 V 3/0 AWG
Cu 200 A - 22,6 Nm*
Al 155 A - 22,6 Nm*


IEC 60947-7-1
IEC 61238-1
1000 V AC/DC 95mm²
Cu 232 A - 19 Nm*
Al 200 A - 22,6 Nm*

* see instruction leaflet



C(7:2)

1SNF526031R0000
PART NO.

5	2	SET_SCREW_M14X20	SET_SCREW_M14X20	-	
4	1	PHILLIPS_SCREW_M4X10	PHILLIPS_SCREW_M4X10	-	
3	1	HOUSING_CBS95_2P	HOUSING_CBS95_2P	-	
2	1	COVER_CBS95_GREEN	COVER_CBS95_GREEN	-	
1	1	ALUMINUM_BLOCK_CBS95_2P	ALUMINUM_BLOCK_CBS95_2P	-	
RPT	QTY	DOC TITLE	DESCRIPTION	ITEM NUMBER	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 2022-02-11 Pavan, Singh	TE Connectivity	
			CHK 2022-02-14 Pavan, Singh		
			APVD 2022-02-14 Saurabh, Bishr		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME CBS95-2P-GREEN	
		0 PLC ±0	APPLICATION SPEC	- SIZE A3CAGE CODE 00779DRAWING NO C-1SNP300335-0300RESTRICTED TO -	
		1 PLC ±1			
		2 PLC ±1			
		3 PLC ±1			
		4 PLC ±1			
MATERIAL		FINISH	WEIGHT	SCALE 11:20SHEET 1 OF 1REV A	
-		-	-		
			CUSTOMER DRAWING		