









P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	14FEB2022	PS	SB



SECTION A-A



SECTION B-B




CBS95-2P...

UL 1059 CSA C22.2 No. 158-10 1000 V 3/0 AWG Cu 200 A - 22,6 Nm* Al 155 A - 22,6 Nm*	IEC 60947-7-1 IEC 61238-1 1000 V AC/DC 95mm ² Cu 232 A - 19 Nm* Al 200 A - 22,6 Nm*
---	--

* see instruction leaflet

C (7:2)

5	2	SET_SCREW_M14X20	SET_SCREW_M14X20	-	
4	1	PHILLIPS_SCREW_M4X10	PHILLIPS_SCREW_M4X10	-	
3	1	HOUSING_CBS95_2P	HOUSING_CBS95_2P	-	
2	1	COVER_CBS95_BLUE	COVER_CBS95_BLUE	-	
1	1	ALUMINUM_BLOCK_CBS95_2P	ALUMINUM_BLOCK_CBS95_2P	-	
RPT	QTY	DOC TITLE	DESCRIPTION	ITEM NUMBER	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 2022-02-11 Pavan, Singh	TE Connectivity	
			CHK 2022-02-14 Pavan, Singh		
			APVD 2022-02-14 Saurabh, Bishr		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME CBS95-2P-BLUE	
		0 PLC ±1	APPLICATION SPEC	- - -	
		1 PLC ±1			
		2 PLC ±1			
		3 PLC ±1			
		4 PLC ±1			
		ANGLES ±1			
MATERIAL		FINISH	WEIGHT	RESTRICTED TO	
-		-	-	-	
		-			
CUSTOMER DRAWING				SCALE 11:20	SHEET 1 OF 1
					REV A

1SNF526021R0000
PART NO.