



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	02JUL2022	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



PRINT COLOR CONFORMS TO LABELING STANDARD TIA-606

All dimensions in mm [Inch]

TE PN: 1SET530108R0000

OUTSIDE WOUND LABEL ACROSS: 3 PER ROLL QTY: 3000

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
4 PLC ±	ANGLES ±
MATERIAL SEE TABLE	FINISH -

MATERIAL	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
LINEAR	WHITE KRAFT
DWN GOPALAKRISHNA HV 02JUL2022	TE Connectivity
CHK D.BURGAT 02JUL2022	
APVD D.BURGAT 02JUL2022	NAME SBP EWS LABEL - YELLOW 25.4 x 57.2mm [1.00 x 2.25inch]
PRODUCT SPEC TTDS-283	
APPLICATION SPEC	
WEIGHT 0.202g	SIZE A2
CUSTOMER DRAWING	CAGE CODE FB1U7
	DRAWING NO C=SBPE12-1925-YL-3
	RESTRICTED TO
	SCALE 1:1
	SHEET 1 OF 1
	REV A