





D

C

B

A



1. CODING IS AS FOLLOWS. SEE TABLE 1.

2. APPLIED RECEPTACLE CONTACT P/N:

DESCRIPTION	2.8mm SENSOR-FLAT RECEPTACLE OR EQUIVALENT
PART NO.	967542 OR EQU 967543 OR EQU
WIRE SIZE	0.5~1.0 >1.0~2.5

3. APPLIED WIRE SEAL P/N:

DESCRIPTION	SINGLE-WIRE SEAL (5mm HOLE)
PART NO.	828904 828905
INSULATION DIA. (Ø)	1.2~2.1mm 2.2~3.0mm

4. LASERPRINT MARK THE PRODUCT PART NUMBER. CHARACTER SIZE APPROX 1.2MM RAISE. CHARACTER LOCATION AND ORIENTATION AS SHOWN
5. LASERPRINT MARK DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY. YEAR: FIRST AND SECOND DIGITS (17=2017) MONTH: THIRD DIGIT, EXCLUDING 1, A=JAN, B=FEB, C=MARCH... (K=OCTOBER) DAY: FOURTH AND FIFTH DIGITS (14=14th DAY) HOUR: SIXTH AND SEVENTH DIGITS (11=11AM)
6. SUPPLY CONDITION: HINGE IN PRELOCKED POSITION
7. SUPPLY CONDITION: CPA IN PRELOCKED POSITION

TABLE 1

CODE 1: 2345390-1	CODE 11: 2345390-2
9.0	5.0

1	1	PC	RED	PA46-GF15	CPA	4
1	1	PC	GREEN	SILICON	INNER SEAL	3
1		PC	YELLOW	PA6-GF25	CODE 11	2
	1	PC	BLUE	PA6-GF25	CODE 1	2
1	1	PC	BLACK	PA6-GF25	HOUSING	1
-2	-1	U/M	COLOR	MATERIAL	DESCRIPTION	ITEM
B	B	REVISION OF EACH ASSY NO.				
5.6	5.6	WEIGHT OF EACH ASSY NO. [g]				
QTY PER ASSY		PARTS LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±5°

FINISH

SEE TABLE

N/A

DWN D.ZHAO 26APR2019

CHK E.JIANG 26APR2019

APVD I.YIN 26APR2019

PRODUCT SPEC 108-32584

APPLICATION SPEC 114-160078

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME SEALED-3P-PLUG-CPA-ASSEMBLY (FLAT SENSOR CONNECTOR)

SIZE A2

CAGE CODE C-2345390

DRAWING NO

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV B