



12

11

10

9

8

7

6

5

4

3

2

1

0.50mm CENTER FLAT FLEX CABLE (FFC) (105°C, Sn PLATED)

"L" DIM. →

30 ± 2 MM

51 ± 2 MM

76 ± 3 MM

102 ± 3 MM

127 ± 4 MM

152 ± 4 MM

178 ± 4 MM

203 ± 4 MM

229 ± 5 MM

254 ± 5 MM

305 ± 5 MM

REF DIM →

(1.18 INCH)

(2 INCHES)

(3 INCHES)

(4 INCHES)

(5 INCHES)

(6 INCHES)

(7 INCHES)

(8 INCHES)

(9 INCHES)

(10 INCHES)

(12 INCHES)

CABLE TYPE →

A

D

A

D

A

D

A

D

A

D

A

D

A

D

A

D

A

D

A

D

A

D

CIRCUITS ↓

7

152660745

152660744

152660747

152660746

152660749

152660748

152660751

152660750

152660753

152660752

152660755

152660754

152660757

152660756

152660759

152660758

152660761

152660760

152660763

152660762

152660765

152660764

9

152660767

152660766

152660769

152660768

152660771

152660770

152660773

152660772

152660775

152660774

152660777

152660776

152660779

152660778

152660781

152660780

152660783

152660782

152660785

152660784

152660787

152660786

11

152660789

152660788

152660791

152660790

152660793

152660792

152660795

152660794

152660797

152660796

152660799

152660798

152660801

152660800

152660803

152660802

152660805

152660804

152660807

152660806

152660809

152660808

13

152660811

152660810

152660813

152660812

152660815

152660814

152660817

152660816

152660819

152660818

152660821

152660820

152660823

152660822

152660825

152660824

152660827

152660826

152660829

152660828

152660831

152660830

15

152660833

152660832

152660835

152660834

152660837

152660836

152660839

152660838

152660841

152660840

152660843

152660842

152660845

152660844

152660847

152660846

152660849

152660848

152660851

152660850

152660853

152660852

17

152660855

152660854

152660857

152660856

152660859

152660858

152660861

152660860

152660863

152660862

152660865

152660864

152660867

152660866

152660869

152660868

152660871

152660870

152660873

152660872

152660875

152660874

19

152660877

152660876

152660879

152660878

152660881

152660880

152660883

152660882

152660885

152660884

152660887

152660886

152660889

152660888

152660891

152660890

152660893

152660892

152660895

152660894

152660897

152660896

21

152660899

152660898

152660901

152660900

152660903

152660902

152660905

152660904

152660907

152660906

152660909

152660908

152660911

152660910

152660913

152660912

152660915

152660914

152660917

152660916

152660919

152660918

23

152660921

152660920

152660923

152660922

152660925

152660924

152660927

152660926

152660929

152660928

152660931

152660930

152660933

152660932

152660935

152660934

152660937

152660936

152660939

152660938

152660941

152660940

25

152660943

152660942

152660945

152660944

152660947

152660946

152660949

152660948

152660951

152660950

152660953

152660952

152660955

152660954

152660957

152660956

152660959

152660958

152660961

152660960

152660963

152660962

27

152660965

152660964

152660967

152660966

152660969

152660968

152660971

152660970

152660973

152660972

152660975

152660974

152660977

152660976

152660979

152660978

152660981

152660980

152660983

152660982

152660985

152660984

29

152660987

152660986

152660989

152660988

152660991

152660990

152660993

152660992

152660995

152660994

152660997

152660996

152660999

152660998

152661001

152661000

152661003

152661002

152661005

152661004

152661007

152661006

31

152661009

152661008

152661011

152661010

152661013

152661012

152661015

152661014

152661017

152661016

152661019

152661018

152661021

152661020

152661023

152661022

152661025

152661024

152661027

152661026

152661029

152661028

33

152661031

152661030

152661033

152661032

152661035

152661034

152661037

152661036

152661039

152661038

152661041

152661040

152661043

152661042

152661045

152661044

152661047

152661046

152661049

152661048

152661051

152661050

35

152661053

152661052

152661055

152661054

152661057

152661056

152661059

152661058

152661061

152661060

152661063

152661062

152661065

152661064

152661067

152661066

152661069

152661068

152661071

152661070

152661073

152661072

37

152661075

152661074

152661077

152661076

152661079

152661078

152661081

152661080

152661083

152661082

152661085

152661084

152661087

152661086

152661089

152661088

152661091

152661090

152661093

152661092

152661095

152661094

39

152661097

152661096

152661099

152661098

152661101

152661100

152661103

152661102

152661105

152661104

152661107

152661106

152661109

152661108

152661111

152661110

152661113

152661112

152661115

152661114

152661117

152661116

41

152661119

152661118

152661121

152661120

152661123

152661122

152661125

152661124

152661127

152661126

152661129

152661128

152661131

152661130

152661133

152661132

152661135

152661134

152661137

152661136

152661139

152661138

43

152661141

152661140

152661143

152661142

152661145

152661144

152661147

152661146

152661149

152661148

152661151

152661150

152661153

152661152

152661155

152661154

152661157

152661156

152661159

152661158

152661161

152661160

45

152661163

152661162

152661165

152661164

152661167

152661166

152661169

152661168

152661171

152661170

152661173

152661172

152661175

152661174

152661177

152661176

152661179

152661178

152661181

152661180

152661183

152661182

47

152661185

152661184

152661187

152661186

152661189

152661188

152661191

152661190

152661193

152661192

152661195

152661194

152661197

152661196

152661199

152661198

152661201

152661200

152661203

152661202

152661205

152661204

49

152661207

152661206

152661209

152661208

152661211

152661210

152661213

152661212

152661215

152661214

152661217

152661216

152661219

152661218

152661221

152661220

152661223

152661222

152661225

152661224

152661227

152661226

0.086 mm POLYESTER + ADHESIVE

0.10 mm COPPER

0.086 mm POLYESTER + ADHESIVE

0.155 mm POLYESTER

CROSS-SECTION

4.00±0.80

0.50±0.12

0.50±0.05

0.5 (N-1) ± 0.07

0.30±0.02

0.50 (N+1) ± 0.06

END TAIL DETAIL

SCALE 10:1

NOTES:

1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

MM

SCALE

NA

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES

±----

±----

3 PLACES

±----

±----

2 PLACES

±----

±----

1 PLACE

±----

±----

0 PLACES

±----

±----

ANGULAR TOL

±

0.5 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

C-SIZE

SERIES

15266

CURRENT REV DESC: STIFFENER LENGTH & SPAN TOLERANCE UPDATED

EC NO: 735490

DRWN: DIEGOG7

CHK'D: JSMITH11

APPR: JSMITH11

2023/01/18

2023/01/26

2023/01/26

INITIAL REVISION:

DRWN: JLWOLFSB

APPR: DRASMUSS

2010/09/24

2010/11/17

0.50MM CENTER FLAT FLEX CABLE (FFC) (105°C, SN PLATED) SALES DRAWING

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SD-15266-001

DOC TYPE

PSD

DOC PART

001

REVISION

D

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

SEE CHART

GENERAL MARKET

2 OF 2

DOCUMENT STATUS

P1

RELEASE DATE

2023/01/26 03:20:41