


NOTES:

1. MATERIALS:
 CONTACT: BERYLLIUM COPPER
 ALL OTHER METAL PARTS: STAINLESS STEEL
 INSULATOR: ULTEM1000
2. FINISH:
 CONTACT: GOLD
 ALL OTHER METAL PARTS: PASSIVATED
3. MECHANICAL/ENVIRONMENTAL:
 DURABILITY: 500 CYCLES
4. ELECTRICAL:
 IMPEDANCE: 50Ω
 FREQUENCY RANGE: DC to 50GHz
 VSWR(dB): 1.2: 1(-20.83dB)



FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED TO GENERAL MARKET			molex			
$\frac{F}{A} = 0$	MM/INCH	NTS		EC NO: 735515 DRWN: KTAGAN 2023/01/18 CHK'D: LMEIER 2023/01/18 APPR: JBORRELLI 2023/01/19			1.85MM JACK TO 2.4MM JACK ADAPTER				
$\frac{F}{C} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)						INITIAL REVISION: DRWN: VISHNM2 2022/11/23 APPR: LMEIER 2022/12/15			PRODUCT CUSTOMER DRAWING	
$\frac{F}{P} = 0$		MM	INCH	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						DOCUMENT NUMBER	
DIVISIONAL SYMBOLS	4 PLACES	±	±				THIRD ANGLE PROJECTION			733862280	
	3 PLACES	±	±	DRAWING		SERIES				MATERIAL NUMBER	
	2 PLACES	±	±	C-SIZE		73386	733862280				1 OF 1
	1 PLACE	±	±								
	0 PLACES	±	±								
	ANGULAR TOL	±	°								