


NOTES:

1. MATERIALS:  
 CONTACT: BERYLLIUM COPPER  
 ALL OTHER METAL PARTS: STAINLESS STEEL  
 INSULATOR: ULTEM1000
2. FINISH:  
 CONTACT: GOLD  
 ALL OTHER METAL PARTS: PASSIVATED
3. MECHANICAL/ENVIRONMENTAL:  
 DURABILITY: 500 CYCLES
4. ELECTRICAL:  
 IMPEDANCE: 50Ω  
 FREQUENCY RANGE: DC to 50GHz  
 VSWR(dB): 1.2:1 (-20.83dB)



FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED TO GENERAL MARKET			<b>molex</b>		
$\frac{F}{A} = 0$	MM/INCH	NTS		EC NO: 735515 DRWN: KTAGAN 2023/01/18 CHK'D: LMEIER 2023/01/18 APPR: JBORRELLI 2023/01/19			2.4MM PLUG TO 2.4MM JACK ADAPTER			
$\frac{F}{C} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)						INITIAL REVISION: DRWN: VISHNM2 2022/11/24 APPR: LMEIER 2022/12/15			PRODUCT CUSTOMER DRAWING
$\frac{F}{P} = 0$		MM	INCH	DOCUMENT NUMBER						DOC TYPE   DOC PART   REVISION
DIVISIONAL SYMBOLS	4 PLACES	±	±				733870050			PSD 000 A1
	3 PLACES	±	±	MATERIAL NUMBER						CUSTOMER
	2 PLACES	±	±				73387			SHEET NUMBER
	1 PLACE	±	±	733870050						
	0 PLACES	±	±				THIRD ANGLE PROJECTION			C-SIZE
	ANGULAR TOL	±	°	DRAWING						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SERIES			SERIES
				SERIES						

DOCUMENT STATUS	P1	RELEASE DATE	2023/01/19	15:06:02
-----------------	----	--------------	------------	----------