




REV	ECN	APP'D
-	4158	JT 10/26/00
A	5571	JT 12/26/00
B	5709	



- NOTES:
- MATERIALS:
BODY AND WIRE SUPPORT: POLYETHERIMIDE PER MIL-P-46184
GROMMET AND SEAL: SILICONE RUBBER PER ZZ-R-765
CONTACT RETAINERS: BERYLLIUM COPPER
CONTACT CONTACTS: COPPER ALLOY, HARD GOLD PLATED PER MIL-G-45204
 - PERFORMANCE SPECIFICATIONS:
OPERATING TEMPERATURE: -65 TO 125 DEG C
INSULATION RESISTANCE: 1000 MEGOHMS MIN
DWV: 1500 VRMS AT SEA LEVEL AND 700 VRMS AT 80,000 FT
VIBRATION AND SHOCK PER MIL-STD-202
 - SOCKET MATES WITH M83536/2-028 AND M83726/24-25 RELAYS

DIMENSIONS ANSI Y14.5M UNITS: INCHES ACAD FILE	TOLERANCES .XX ±.01 .XXX ±.005 ANGLES ±2°	PROJECTION 	Amphenol Pcd SPECIFICATION DRAWING					
			ENGR MEL 10/25/00					
			CHKD J. TON 12/26/00					
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC. PEABODY, MA		APPD A. PATRIE 10/26/00		TITLE TRACK MOUNT RELAY SOCKET M12883/52-001			REV B
			SIZE B					
			CODE: 58982	SCALE: NONE				