


ITEM	PART#	DESCRIPTION	QTY	UOM
A,B	5024390200	2.0 W/B Single Plug Hsg 2Ckt	2	PC
C	5024380000	2.0 W/B Single Plug Term W/Plt Chain	4	PC
D	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	B1	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	B2	1X22AWG DISC SR-PVC BK UL10002	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2219581020	Clik-Mate 2.0 R-R 2ckt 50mm disc Sn	50±5	15
2219581021	Clik-Mate 2.0 R-R 2ckt 100mm disc Sn	100±5	15
2219581022	Clik-Mate 2.0 R-R 2ckt 150mm disc Sn	150±5	15
2219581023	Clik-Mate 2.0 R-R 2ckt 300mm disc Sn	300±5	15
2219581024	Clik-Mate 2.0 R-R 2ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

- NOTES
1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 3. LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 4. LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/02/12	A	INITIAL RELEASE	THANUB

DOCUMENT STATUS	P1	RELEASE DATE	2022/12/23	12:42:16
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS $\nabla_A = 0$ $\nabla_E = 0$ $\nabla_P = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		<p>SEE TABLE</p> <p>PRODUCT CUSTOMER DRAWING</p>
	DIMENSION UNITS	SCALE	EC NO: 732309		
	mm	NTS	DRWN: THANUB 2022/12/02		
	GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: SKUMAR07 2022/12/23		
ANGULAR TOL ± °		APPR: SKUMAR07 2022/12/23		DOCUMENT NUMBER	
4 PLACES ±		INITIAL REVISION:		2219581020	
3 PLACES ±		DRWN: THANUB 2022/12/02		PSD 000 A	
2 PLACES ±		APPR: SKUMAR07 2022/12/23		DOC TYPE DOC PART REVISION	
1 PLACE ±		DRWN: THANUB 2022/12/02		2219581020 PSD 000 A	
0 PLACES ±		APPR: SKUMAR07 2022/12/23		MATERIAL NUMBER CUSTOMER SHEET NUMBER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	SEE TABLE GENERAL MARKET 1 OF 1