



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	13JUL2023	C.K	H.L







NOTES:

1. MATERIAL: PBT UL94V-0.
2. COMPATIBLE CONTACT: 2420268-X.
3. MATING PARTS: X-2420265-X,
X-2423324-X



△ TRADE MARK : TE

CIRCUITS	COLOUR	KEYING	P/N	DIMENSIONS(mm)		
				A	B	C
2	LIGHT BLUE	A	2420266-2	8.7	4.0	2.7
	YELLOW	B	2-2420266-2	8.7	4.0	2.7
	RED	C	3-2420266-2	8.7	4.0	2.7
3	LIGHT BLUE	A	2420266-3	12.7	8.0	6.65
	YELLOW	B	2-2420266-3	12.7	8.0	6.65
	RED	C	3-2420266-3	12.7	8.0	6.65
4	LIGHT BLUE	A	2420266-4	16.7	12.0	7.2
	YELLOW	B	2-2420266-4	16.7	12.0	7.2
	RED	C	3-2420266-4	16.7	12.0	7.2
5	LIGHT BLUE	/	2420266-5	20.7	16.0	6.65






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CONNOR KANG 20DEC2022		 TE Connectivity Ltd.	
DIMENSIONS: mm		CHK HOPE LU 20DEC2022			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD LU HOPE 10JUN2022		NAME HCI 4.0 PITCH WTB SOCKET HSG	
		PRODUCT SPEC 108-160771 APPLICATION SPEC 114-160464		SIZE A3	
0 PLC ± - 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± -		WEIGHT -		CAGE CODE 00779	
MATERIAL -		FINISH -		DRAWING NO C-2420266	
CUSTOMER DRAWING				RESTRICTED TO -	
				SCALE N.T.S.	
				SHEET 1 OF 5	
				REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




CIRCUITS	COLOUR	KEYING	P/N	DIMENSIONS(mm)			
				A	B	C	D
6	LIGHT BLUE	/	2420266-6	12.7	8.0	6.65	/
8	LIGHT BLUE	/	2420266-8	16.7	12.0	7.2	11.9
10	LIGHT BLUE	/	1-2420266-0	20.7	16.0	6.65	11.45
12	LIGHT BLUE	/	1-2420266-2	24.7	20.0	7.2	11.9
14	LIGHT BLUE	/	1-2420266-4	28.7	24.0	6.65	11.45



NOTES:

- NOTES:
1. MATERIAL: PBT UL94V-0.
 2. COMPATIBLE CONTACT: 2420268-X.
 3. MATING PARTS: X-2420265-X,
X-2423324-X

 TRADE MARK : TE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CONNOR KANG 20DEC2022		 TE Connectivity Ltd.	
		CHK HOPE LU 20DEC2022			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HCI 4.0 PITCH WTB SOCKET HSG	
		0 PLC ± — 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± — 4 PLC ± — ANGLES ± —			
MATERIAL —		FINISH —		SIZE CAGE CODE DRAWING NO RESTRICTED T	
		WEIGHT —		A3 00779 C-2420266 —	
CUSTOMER DRAWING				SCALE 1:1	SHEET 2 OF 5
				REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

TYPE A

TYPE B







TYPE C

6P




8P

10P


2P




3P






12P




14P



4P



5P



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CONNOR KANG 20DEC2022	 TE Connectivity Ltd.		
		CHK HOPE LU 20DEC2022			
		APVD HOPE LU 20DEC2022	NAME HCI 4.0 PITCH WTB SOCKET HSG		
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-2420266
		CUSTOMER DRAWING		SCALE 1:1	SHEET 3 of 5
				REV A	RESTRICTED TO —

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




FIGURE 1







FIGURE 3





FIGURE 4





FIGURE 5





FIGURE 6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CONNOR KANG 20DEC2022	 TE Connectivity Ltd.			
		CHK HOPE LU 20DEC2022				
DIMENSIONS: mm		APVD HOPE LU 20DEC2022	NAME HCI 4.0 PITCH WTB SOCKET HSG			
		PRODUCT SPEC —	—			RESTRICTED TO —
		APPLICATION SPEC —	—			
		SIZE	CAGE CODE	DRAWING NO		
		A3 00779		C-2420266		
MATERIAL —		WEIGHT —				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± — 4 PLC ± — ANGLES ± —		CUSTOMER DRAWING				
FINISH —		SCALE 1:1		SHEET 4 of 5		REV A


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

PACKAGE LIST

TE P/N	PE BAG	Q' TY	Q' TY
X-2420266-2	500 PCS	2500 PCS	10000 PCS
X-2420266-3	300 PCS	1500 PCS	6000 PCS
X-2420266-4	200 PCS	1000 PCS	4000 PCS
X-2420266-5	200 PCS	1000 PCS	4000 PCS
X-2420266-6	200 PCS	1000 PCS	4000 PCS
X-2420266-8	200 PCS	1000 PCS	4000 PCS
1-2420266-0	150 PCS	750 PCS	3000 PCS
1-2420266-2	150 PCS	750 PCS	3000 PCS
1-2420266-4	100 PCS	500 PCS	2000 PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± 0.30

2 PLC ± 0.20

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

DWN
CONNOR KANG
20DEC2022

CHK
HOPE LU
20DEC2022

APVD
HOPE LU
20DEC2022

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

 TE Connectivity Ltd.

NAME
HCI 4.0 PITCH WTB SOCKET HSG
—

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2420266

RESTRICTED TO
—

SCALE
1:1

SHEET
5 of 5

REV
A

1470-19 (1/15)