






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	31MAY2022	F.Z	R.B
	B		16APR2024	R.W	R.B


















10POS PN: 1-2394617-0


1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC POLYSTER(UL94V-0),COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY
2. FINISH (ALL OVER): NICKEL PLATING 1.27umMIN.
3. FINISH (CONTACT TAB):GOLD PLATING: 0.38umMIN.
(CONTACT TAIL): TIN PLATING: 1.0umMIN.
4. THE KEYING ARRANGEMENTOF "Y" IS SYMMETIC WITH "X"
5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOWN THE OUTLINE, AND DON'T SHOWN DETAIL

16	Y	15	30.0	33.0	34.6	2-2394617-3
16	X	15	30.0	33.0	34.6	1-2394617-3
10	Y	9	18.0	21.0	22.6	2-2394617-0
10	X	9	18.0	21.0	22.6	1-2394617-0
8	Y	7	14.0	17.0	18.6	2-2394617-8
8	X	7	14.0	17.0	18.6	1-2394617-8
4	Y	3	6.0	9.0	10.6	2-2394617-4
4	X	3	6.0	9.0	10.6	1-2394617-4
POS	KEY	n	A	B	C	PART NO


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 31MAY2022 FISHER ZHU		
		CHK 31MAY2022 RICK BIAN		
DIMENSIONS: mm		APVD 31MAY2022 RICK BIAN	NAME DYNAMIC D1100 SERIES HDR ASSY, 4-10POS, V-TYPE, AU-PL	
		PRODUCT SPEC 108-78268	SIZE	
		APPLICATION SPEC 114-5377	CAGE CODE	
MATERIAL		WEIGHT	DRAWING NO	
			RESTRICTED TO	
		CUSTOMER DRAWING	SCALE 2:1	
			SHEET 1 OF 3	
			REV B	


P	LTR	DESCRIPTION	DATE	DWN	APVD



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 31MAY2022		 TE Connectivity	
DIMENSIONS: mm		CHK RICK BIAN 31MAY2022			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RICK BIAN 31MAY2022	
		0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3°		PRODUCT SPEC SEE SHEET1/2	
MATERIAL		FINISH		APPLICATION SPEC SEE SHEET1/2	
		WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		-	
		SCALE 4:1		SHEET 2 OF 3	
		REV B			

P	LTR	DESCRIPTION	DATE	DWN	APVD



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 31MAY2022	 TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK RICK BIAN 31MAY2022	NAME DYNAMIC D1100 SERIES HDR ASSY, 4-10POS, V-TYPE, AU-PL -			
	0 PLC ±0.3	APVD RICK BIAN 31MAY2022				
	1 PLC ±0.3	PRODUCT SPEC SEE SHEET1/2				
	2 PLC ±0.3	APPLICATION SPEC SEE SHEET1/2				
MATERIAL	3 PLC ±0.3	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -
	4 PLC ±0.3	CUSTOMER DRAWING	A3	00779	C-2394617	
	ANGLES ±3°					
		SCALE 2:1		SHEET 3 OF 3		REV B