





A

C

D

PRODUCT NUMBER	DIM A(mm)
10176873-A8-F587LF	1500±30
10176873-A8-F588LF	2500±50
10176873-A8-F589LF	3500±70
10176873-A8-F590LF	4500±90
10176873-A8-F591LF	5500±110
10176873-A8-F592LF	6500±130

Detail A
Scale 4:1

- NOTE:
- ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
 - UNLESS OTHERWISE SPECIFIED ASSEMBLED LENGTH TOLERANCE =
< 1 METER: ±15.0mm
1 METER TO 10 METER: ±2% OF "DIM L"
> 10 METER: +0.00%-4% OF "DIM L"
 - CONNECTOR ASSEMBLIES SHOWN ARE FOR REFERENCE ONLY AND MAY NOT SHOW ALL PART DETAIL. REFERENCE CONNECTOR HOUSING DRAWINGS FOR COMPLETE DETAILS.
 - COMPLIANT TO THE CURRENT ROHS DIRECTIVE.

spec ref	dr	Garry Cao	01/12'26	Amphenol Power Solutions A Division of Amphenol Corporation amphenol-icc.com	scale	MM	size	NA	A3
tolerance std	eng	Garry Cao	01/12'26		ecr no				
surface	rvwr	Andy Zhuang	01/12'26		rel level				
	appr	Siny Hu	01/12'26		cat. no.				
	projection				title	60A 7PIN AC WHIP CABLE ASSEMBLY	rev	A	
		product family	Product - Customer Drw		sheet 1 of 1				