






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	22SEP2025	M,S	J.M




Requires Housing X-2511766-X


The product using material and processing must conform to the “WI-PZ-142”HSF technical standard control requirements

TC PN	Wire Range	Insulation O.D.	Material	Finish
2511767-1	AWG #28~#32	0.80mm(max)	Phosphor Bronze	Ni 1.27 μ m [50u”Min],Au - Flash
2511767-2	AWG #28~#32	0.80mm(max)	Phosphor Bronze	Ni 1.27 μ m [50u”Min],0.38 μ m[15u”]Au
2511767-3	AWG #28~#32	0.80mm(max)	Phosphor Bronze	Ni 1.27 μ m [50u”Min],2 μ m[80u”]Matte Tin
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRATHAP SK 01JUL2025	TE Connectivity	
		CHK MADHAN S 01JUL2025		
		APVD JAGRUTI M 03SEP2025	NAME	
		PRODUCT SPEC 108-162162	1MM 2ROW INT LCKNG HPI TERMINAL	
		APPLICATION SPEC 114-161614		
		WEIGHT 0	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 2
			REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—




TERMINAL



paper tray (Ø480mm)

adhesive tape





angle bead

Load carton



Sealed carton



desiccant

TC PN	Qty/reel	Qty/Box
2511767-1	20000 PCS	140000 PCS
2511767-2	20000 PCS	140000 PCS
2511767-1	20000 PCS	140000 PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRATHAP_SK 01JUL2025	TE Connectivity		
		CHK MADHAN_S 01JUL2025			
DIMENSIONS: mm [INCHES]		APVD JAGRUTI_M 03SEP2025	NAME — 1MM 2ROW INT LCKNG HPI TERMINAL —		
		PRODUCT SPEC 108-162162	SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C=2511767 —		
		APPLICATION SPEC 114-161614			
MATERIAL SEE TABLE		WEIGHT —	CUSTOMER DRAWING SCALE 1:1 SHEET 2 OF 2 REV A		
FINISH SEE TABLE					