




PH CONNECTOR



2.0mm Pitch/Disconnectable Crimp Style Connectors



Part Number:

- ASPHSPH24R305

Description:

- JST Series – PH Series
- Pitch – 2mm
- Cable length (inside dimension) – 305mm

Material Specification:

- (1) Terminal: SPH-002T-P0.5S
- (2) Cable Type: UL1007
- (2) Cable Size: 24AWG
- (2) Cable Colour: Red

Accessories:

- Extraction Tool: EJ-PH

Quality

- We trust and believe in our product. Each step of our development and manufacturing process is focused on delivering a fault-free product. JST does not compromise on quality.

Applicable Housings:

No. of Circuits	Part Number
2	PHR-2
3	PHR-3
4	PHR-4
5	PHR-5
6	PHR-6
7	PHR-7
8	PHR-8
9	PHR-9
10	PHR-10
11	PHR-11
12	PHR-12
13	PHR-13
14	PHR-14
15	PHR-15
16	PHR-16

Additional Information:


Alternative Colours and length cables are available upon request, please contact JST for further details by e-mailing jukma@jst.co.uk



PH CONNECTOR

JST
The Quality Connection

2.0mm Pitch/Disconnectable Crimp Style Connectors



A SPH SPH 24 R 305

Supply Form: Assembled Wire

Terminal Part Number end A: SPH-002T-P0.5S

Terminal Part Number end B: SPH-002T-P0.5S

Cable Size: 24awg (??AWG)

Cable Colour: B (Blue), K (Black), R (Red), N (Brown), H (Grey)
O (Orange), Y (Yellow), W (White), M (Green), P (Purple), PK (Pink)

Cable Length: 305mm (????mm)

Additional Information:

Alternative Colours and length cables are available upon request, please contact JST for further details by e-mailing jukma@jst.co.uk