






AMPHENOL PN
10197766-1030LF



WIRING LIST		
CON1		CON2
PIN1	RED	PIN1
PIN2	GRAY	PIN2
PIN3	GRAY	PIN3
PIN4	GRAY	PIN4
	•	
	•	
	•	
PIN9	GRAY	PIN9
PIN10	GRAY	PIN10

NOTES:

- ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
- UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE TESTED:
HI-POT: DC 300V/10ms.
DIELECTRIC RESISTANCE: 10M Ohms MIN.
CONNECTION RESISTANCE: 3 Ohms MAX.
- LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES.

/	M	Flat Cable, UL2678, 30AWG*10C, PITCH: 0.635MM															2	
2	EA	IDC CONN.: 1.27PITCH, 2X5PIN, 0.25um GOLD AT CONTACT, BLACK, 20021444-00010T4LF															1	
Qty	Unit	Description															Item	
mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		Cable Assembly								
ltr	ecn no	dr	date	tolerances unless otherwise specified						title IDC CABLE ASSEMBLY								
A		Jacob	3/23'26	angles		linear											scale N/A	
				dr	Jacob Ding		3/23'26				dwg no		sheet 1 of 1		size			
				enr	Jacob Ding		3/23'26				10197766-1030LF		A3					
				chr	TIM YAO		3/23'26											
				appd	TIM YAO		3/23'26				type		Customer		Drawing			
sheet index	revision sheet	A																