





- Dynamic installation: $-5^{\circ}\text{C} \dots +70^{\circ}\text{C}$

Loading Plan

1	wire 1
2	wire 2
3	wire 3
PE	green/yellow



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
0.2	XXX=002	
Step	a [m]	XXX

Ölflex 409 P 4G1,5mm², PUR, black	33400300204XXX
Type of cable	Part no.

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
		All rights reserved Department HCS - GPM		Created by COSTEA Costeia		Inspected by COSTEA Costeia		Standardisation BANCIUD Banciu	
HARTING Customised Solutions D-32339 Espelkamp		Title Han 1A OM 3+PE +latch f/- PUR						Date 2024-04-24	
								State Final Release	
								Doc-Key / ECM-Nr. 101132509/UGD/001/A 500000268092	
		Type TB		Number 33400300204XXX				Rev. A	
								Page 1/1	