

Drawing shown for below
2528102


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	Production Release	06FEB2026	MS	JM

- SPECIFICATIONS
- A. MATERIAL: LEAD-FREE BRASS, THE LEAD CONTENT MUST BE LESS THAN 100PPM
PLATING: COMPOSITE COATING, OVERALL SURFACE PLATED WITH PLATINUM AT A THICKNESS OF 0.25 MICROMETERS.
 - B. ENVIRONMENTAL
 - 1) STORAGE AND OPERATING TEMPERATURE RANGE: -40°C~+85°C
 - 2) HUMIDITY RANGE: 10% RH TO 90% RH
 - 3) SALT SPRAY: 48H
 - C. OTHERS
 - 1) PRODUCTS MUST COMPLY WITH ROHS2.0,REACH,CA65 REQUIREMENTS

Note:

DIMENSION A is Customizable to customer needs
DIMENSION B : DIM A + 1.33 MM

- The contact pad surface must be free from appearance defects such as convex points, rough tool marks, and scratches.
- Film Thickness Test Point




RECOMMEND PCB LAYOUT
Layout Tolerance: $\pm 0.02\text{mm}$
Recommended PCB thickness 0.80mm


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRATHAP SK 07JAN2026	TE Connectivity Ltd.		
DIMENSIONS: mm		CHK MADHAN S 07JAN2026			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JAGRUTI M 07JAN2026	NAME		
0 PLC ± 0.35 1 PLC ± 0.15 2 PLC ± 0.10 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$		PRODUCT SPEC 108-162422	CONTACT PAD DIA 16.33MM THMT -		
MATERIAL SEE NOTE		FINISH -	WEIGHT 0	SIZE A2	CAGE CODE 00779
				DRAWING NO C=2528102	RESTRICTED TO -
				SCALE 1:1	SHEET 1 OF 2
				REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

ITRM	W	A0	B0	K0	P	F	E	D	P0	P2	T	13"
DIM	16.0	1.77	1.77	2.80	8.0	7.50	1.75	1.50	4.00	2.00	0.35	Length/Disk
TOLE	+0.30 -0.30	+0.15 -0.15	+0.15 -0.15	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.00	+0.10 -0.10	+0.10 -0.10	+0.05 -0.05	Components/Disk
												23.71M 2900pcs




(A)




(B)


Four triangle Cardboards





waterproof bag




(C)



Each one piece of pearl cotton at top and bottom




Label



(D)

Quantity:2900 * 2 Reel
1PCS: 0.01286 g
PPQ: 0.455 kg
APQ: 1.08 kg
LxWxH: 340*340*315 mm

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 07JAN2026 CHK 07JAN2026 PRATHAP SK MADHAN S		 TE Connectivity Ltd.				
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD 07JAN2026 JAGRUTI M	NAME CONTACT PAD DIA 16.33MM THMT —				
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-162422					
		—		APPLICATION SPEC					
MATERIAL SEE TABLE		FINISH —		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=2528102	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE 1:1		SHEET 2 of 2	REV A	