


PART NUMBER	CABLE ASSY P/N	LENGTH	REV	ECO	DATE
415-0550-050	415-0550-050P	50mm	1	INITIAL RELEASE	04/06/2023
415-0550-100	415-0550-100P	100mm			
415-0550-150	415-0550-150P	150mm			
415-0550-200	415-0550-200P	200mm			
415-0550-250	415-0550-250P	250mm			
415-0550-300	415-0550-300P	300mm			
415-0550-500	415-0550-500P	500mm			



- NOTE:
- 1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 200 VRMS.
 - 2. REFERENCE CONNECTOR ORIENTATION AS SHOWN.
 - 3. ASSEMBLIES 415-0550-XXXX TO BE BULK PACKED.
ASSEMBLIES 415-0550-XXX TO BE PACKAGED 5 PER BAG.

PART LIST		
ITEM	QTY	DESCRIPTION
1	2	MHF4L, GOLD PLATING
2	AR	0.81CABLE, BLACK

 THIS PROPRIETARY DOCUMENT IS PROPERTY OF CINCH CONNECTIVITY SOLUTIONS. IT IS CONFIDENTIAL IN NATURE, NON-TRANSFERABLE, AND ISSUED WITH THE CLEAR UNDERSTANDING THAT IT IS NOT TO BE TRACED OR COPIED WITHOUT PERMISSION AND IS RETURNABLE UPON DEMAND. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No:		415-0550-001/999		JOHNSON					
	RoHS ☒ (EU) 2015/863 COMPLIANT UNLESS OTHERWISE SPECIFIED UNITS: MM .X ±0.2 .XX ±0.08 ANGLES ±	Cage Code	Title:							
		3RD ANGLE PROJECTION 	CABLE ASSY, XMC-6 TO XMC-6							
			Drawing No.	415-0550-001/999			REV.			
			Drawn by:	TOMMY REN			1			
Date:		04/06/2023		Size	B	DO NOT SCALE DRAWING	Workmanship Std:	NONE	Sheet	1 OF 1