


PART NUMBER	CABLE ASSY P/N	LENGTH
415-0551-150	415-0551-150P	150mm
415-0551-250	415-0551-250P	250mm

REV	ECO	DATE
1	INITIAL RELEASE	06/19/2024



- NOTE:
- 1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 200 VRMS.
 - 2. REFERENCE CONNECTOR ORIENTATION AS SHOWN.
 - 3. ASSEMBLIES 415-0551-XXXP TO BE BULK PACKED.
ASSEMBLIES 415-0551-XXX TO BE PACKAGED 5 PER BAG.

PART LIST		
ITEM	QTY	DESCRIPTION
1	1	MHF4L, GOLD PLATING
2	AR	0.81CABLE, BLACK
3	AR	HEAT SHRINK TUBE
4	1	SMA PLUG, GOLD PLATING

 This PROPRIETARY document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No: 415-0551-001/999		JOHNSON		
	RoHS (EU)/2015/863 COMPLIANT	Cage Code	Title: CABLE ASSY, XMC-6 TO SMA STRAIGHT PLUG		
		3RD ANGLE PROJECTION			
	UNLESS OTHERWISE SPECIFIED UNITS: MM .X ±0.2 .XX ±0.08 ANGLES ±	Drawn by: TOMMY REN Date: 06/19/2024	Drawing No. 415-0551-001/999	REV. 1	
		Size B	DO NOT SCALE DRAWING	Workmanship Std: NONE	Sheet 1 OF 1