



PART NUMBER	CABLE ASSY P/N	LENGTH
415-0552-150	415-0552-150P	150mm
415-0552-250	415-0552-250P	250mm

REV	ECO	DATE
1	INITIAL RELEASE	06/19/2024



NOTE:

- CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 200 VRMS.
- REFERENCE CONNECTOR ORIENTATION AS SHOWN.
- ASSEMBLIES 415-0552-XXXP TO BE BULK PACKED.
ASSEMBLIES 415-0552-XXX TO BE PACKAGED 5 PER BAG.



RECOMMENDED MOUNTING HOLE

PART LIST		
ITEM	QTY	DESCRIPTION
1	1	MHF4L, GOLD PLATING
2	AR	0.81CABLE, BLACK
3	AR	HEAT SHRINK TUBE
4	1	WASHER, GOLD PLATING
5	1	NUT, GOLD PLATING
6	1	SMA JACK, GOLD PLATING

 This PROPRIETARY document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No: 415-0552-001/999		JOHNSON			
	RoHS ☒ (EU) 2015/863 COMPLIANT UNLESS OTHERWISE SPECIFIED UNITS: MM .X ±0.2 .XX ±0.08 ANGLES ±	Cage Code	Title: CABLE ASSY, XMC-6 TO SMA STRAIGHT BULKHEAD JACK			
		3RD ANGLE PROJECTION	Drawing No. 415-0552-001/999			
			REV. 1			
		Drawn by: TOMMY REN				
Date: 06/19/2024		Size B	DO NOT SCALE DRAWING	Workmanship Std: NONE	Sheet 1 OF 1	