


PART NUMBER	CABLE ASSY P/N	LENGTH	REV	ECO	DATE
415-0560-050	415-0560-050P	50mm	1	INITIAL RELEASE	04/06/2023
415-0560-100	415-0560-100P	100mm			
415-0560-150	415-0560-150P	150mm			
415-0560-200	415-0560-200P	200mm			
415-0560-250	415-0560-250P	250mm			
415-0560-300	415-0560-300P	300mm			
415-0560-500	415-0560-500P	500mm			



- NOTE:
- 1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 200 VRMS.
 - 2. REFERENCE CONNECTOR ORIENTATION AS SHOWN.
 - 3. ASSEMBLIES 415-0560-XXXP TO BE BULK PACKED.
ASSEMBLIES 415-0560-XXX TO BE PACKAGED 5 PER BAG.

PART LIST		
ITEM	QTY	DESCRIPTION
1	2	MHF4L GOLD PLATING
2	AR	0.81CABLE, BLACK



This PROPRIETARY document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.

Model No:
415-0560-001/999

RoHS (EU)/2015/863 COMPLIANT

UNLESS OTHERWISE SPECIFIED UNITS: MM

.X ±0.2
.XX ±0.08
ANGLES ±

Cage Code

3RD ANGLE PROJECTION

Drawn by:
TOMMY REN

Date:
04/06/2023

Title:
CABLE ASSY, XMC-9 TO XMC-9

Drawing No.
415-0560-001/999

REV.
1

Size B

DO NOT SCALE DRAWING

Workmanship Std: NONE

Sheet 1 OF 1