


PART NUMBER	CABLE ASSY P/N	LENGTH	REV	ECO	DATE
415-0561-150	415-0561-150P	150mm	1	INITIAL RELEASE	06/19/2024
415-0561-250	415-0561-250P	250mm			



- NOTE:
- 1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 200 VRMS.
 - 2. REFERENCE CONNECTOR ORIENTATION AS SHOWN.
 - 3. ASSEMBLIES 415-0561-XXXP TO BE BULK PACKED.
ASSEMBLIES 415-0561-XXX TO BE PACKAGED 5 PER BAG.

PART LIST		
ITEM	QTY	DESCRIPTION
1	1	MHF4L, GOLD PLATING
2	AR	0.81CABLE, BLACK
3	AR	HEAT SHRINK TUBE
4	1	SMA PLUG, GOLD PLATING

 THIS PROPRIETARY DOCUMENT IS PROPERTY OF CINCH CONNECTIVITY SOLUTIONS. IT IS CONFIDENTIAL IN NATURE, NON-TRANSFERABLE, AND ISSUED WITH THE CLEAR UNDERSTANDING THAT IT IS NOT TO BE TRACED OR COPIED WITH- OUT PERMISSION AND IS RETURNABLE UPON DEMAND. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No: 415-0561-001/999		JOHNSON		
	RoHS ☒ (EU) 2015/863 COMPLIANT	Cage Code	Title: CABLE ASSY, XMC-9 TO SMA STRAIGHT PLUG		
		3RD ANGLE PROJECTION 			
	UNLESS OTHERWISE SPECIFIED UNITS: MM .X ±0.2 .XX ±0.08 ANGLES ±	Drawn by: TOMMY REN	Drawing No. 415-0561-001/999	REV. 1	
	Date: 06/19/2024	Size B	DO NOT SCALE DRAWING	Workmanship Std: NONE	Sheet 1 OF 1