



PART NUMBER	CABLE ASSY P/N	LENGTH	REV	ECO	DATE
415-0562-150	415-0562-150P	150mm	1	INITIAL RELEASE	06/19/2024
415-0562-250	415-0562-250P	250mm			



NOTE:

1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 200 VRMS.
2. REFERENCE CONNECTOR ORIENTATION AS SHOWN.
3. ASSEMBLIES 415-0562-XXXP TO BE BULK PACKED.
ASSEMBLIES 415-0562-XXX TO BE PACKAGED 5 PER BAG.



RECOMMENDED MOUNTING HOLE

PART LIST		
ITEM	QTY	DESCRIPTION
1	1	MHF4L, GOLD PLATING
2	AR	0.81CABLE, BLACK
3	AR	HEAT SHRINK TUBE
4	1	WASHER, GOLD PLATING
5	1	NUT, GOLD PLATING
6	1	SMA JACK, GOLD PLATING

 This PROPRIETARY document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No: 415-0562-001/999	JOHNSON		
	RoHS (EU)/2015/863 COMPLIANT	Cage Code	Title: CABLE ASSY, XMC-9 TO SMA STRAIGHT BULKHEAD JACK	
	UNLESS OTHERWISE SPECIFIED UNITS: MM	3RD ANGLE PROJECTION	Drawing No. 415-0562-001/999	REV. 1
	.X ±0.2 .XX ±0.08 ANGLES ±	Drawn by: TOMMY REN Date: 06/19/2024	Size B	DO NOT SCALE DRAWING
			Workmanship Std: NONE	Sheet 1 OF 1