



C-LVRC20PC01S

REV	ECN	DESCRIPTION	DATE	MODIFIED
A	C3003	RELEASE		LUIK.PENG





Amphenol PCD SZ
ORIGINAL
PDF Format
R&D



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受控文件

2018年10月11日



✦: IS CRITICAL CHARACTERISTIC SYMBOL, ◎: IS IMPORTANT CHARACTERISTIC SYMBOL.

NOTES:

- ✦ 1. MATERIAL: CONTACT BODY: COPPER ALLOY; T=0.25mm, CLIP: STAINLESS STEEL, T=0.15mm.
2. CONTACT BODY PLATING: TIN PLATING.
- ◎ 3. WIRE RANGE: 22~18AWG(0.3~0.75 SQ MM), WIRE INSULATION OD RANGE: FROM 1.35MM TO 2.5MM.
- ✦ 4. ROHS COMPLIANCE.
5. REEL PACKING, 3000PCS PER REEL.

DIMENSIONS		TOLERANCES		PROJECTION		TITLE						
ANSI Y14.5M		.X ±0.5				FEMALE CONTACT Ø1.0						
UNITS: MM		.XX ±0.05				FOR 0.3~0.75MM^2						
Pro/E FILE		ANGLES ±3.0°										
ORIGINAL						CHKD		LUIK.PENG Mar-28-18				
						APPD						
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN						SIZE		DWG NO.		REV		
						A3		C-LVRC20PC01S		A		
						CODE: 58982		SCALE: 6:1		SHEET 1 OF 1		