



Amphenol PCD SZ
ORIGINAL
PDF Format
R&D


安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受控文件

2019年7月30日



REV	ECN	DESCRIPTION	DATE	MODIFIED
A		RELEASE	Jul-29-19	





A(3:1)

HVSL362022TA SHOWN IN THIS SHEET

- NOTES:
- 1.SIGNAL CONTACT SHOULD BE ORDERED SEPERATELY
THE SIGNAL CONTACT P/N IS C310003614S,USE LEVER IS 2PCS
 - 2.TIGHT TORQUE WITH MOUNTING PLATE IS 2N.M
 3. $\star$ IS CRITICAL CHARACTERISTICAL SYMBOL
 $\odot$ IS IMPORTANT CHARACTERISTICAL SYMBOL

TECHNICAL DATA		SPECIAL CHARACTERISTICS SYMBOL
VOLTAGE	1000V AC&DC	$\star$
WITHSTAND VOLTAGE	3000V AC	$\star$
INSULATION RESISTANCE	>200 M Ω	$\star$
RATED CURRENT	60A Max@10mm ²	$\star$
WATER PROOF MATED CONDITION	IP67&IP6K9K	$\star$
IP FOR FINGER TOUCH UNMATED CONDITION	IP2XB	$\star$
SHIELDING FUNCTION	YES	NA
MAX MATING CYCLES	50 CYCLES	$\odot$
OPERATING TEMP.	-40-125°C	NA




RECOMMENEED MOUNTING PLATE
THICKNESS 3.0mm Min

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE				
ANSI Y14.5M	.X ±0.5		ENGR		2PIN BUSBAR RECEPTACLE				
UNITS: MM	.XX ±0.05		Rock Jan-10-19						
Pro/E FILE	ANGLES ±2.0°								
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN		CHKD		SIZE	DWG NO.		REV	
			APPD		A3	C-HVSL362022TX		A	
					CODE: 58982		SCALE:3:1	SHEET 1 OF 2	


安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受 控 文 件

2019年7月30日



HVSL362022TA



HVSL362022TB

C-HVSL362022TX

C-HVSL362022TX

SIZE	DWG NO.	REV
A3	C-HVSL362022TX	A
CODE: 58982	SCALE:3:1	SHEET 2 OF 2