


DESCRIPTION: 180 SERIES - STAMPED CONTACTS - MALE


NOTES:

MATERIAL:	PHOSPHOR BRONZE
PLATING:	SEE P/N KEY
WIRE SIZE:	24-26 AWG
CONTACT RESISTANCE:	20 mOHMS MAX.
CONTACT AMPERAGE RATING:	3 AMPS









FOR CLARITY
HIDDEN LINES
NOT SHOWN

180-Y01-170L001

SERIES
TYPE
0 = REEL (10,000 per reel)
1 = LOOSE (500 per bag)
GENDER
1 = MALE
PLATING
1 = SELECTIVE / 10µ" MATING AREA / NICKEL CRIMP AREA
3 = SELECTIVE / 50µ" MATING AREA / NICKEL CRIMP AREA

RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:	J. KADEL
DATE:	09/03/2019

NorComp

SCALE: NTS	SHEET 1 OF 2	REV 2
DWG NO. 180-Y01-170L001		

DESCRIPTION: 180 SERIES - STAMPED CONTACTS - MALE



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: J. KADEL

DATE: 09/03/2019

NorComp

SCALE: NTS

SHEET 2 OF 2

REV 2

DWG NO. 180-Y01-170L001