



MALE FACE VIEW		
1-BLACK 2-WHITE	1-BLACK 2-WHITE 3-GREEN	1-BLACK 2-GREEN 3-RED 4-WHITE



POLES	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
3	1300030026	32357	12 IN [0.3 M]
4	1300030051	32680	12 IN [0.3 M]



MALE FACE VIEW

1. MATERIAL: AS NOTED
2. FINISH: AS NOTED
3. ELECTRICAL:
 - VOLTAGE: 600V AC/DC
 - CURRENT: 2P & 3P : 25A
 - 4P : 20A
4. TEMP RATING: -20°C TO +105°C (A1)
5. PROTECTION: IP67 (WHEN MATED)
6. UL RECOGNIZED FILE: E46237 (A1)
CSA CERTIFIED FILE: LR6837
7. ASSEMBLY IS ROHS COMPLIANT WITH EXEMPTION
8. ALL DIMS ARE FOR REFERENCE UNLESS TOLERANCED OR NOTED OTHERWISE

7	FLAG LABEL	VINYL	YELLOW
6	LOCKNUT	STEEL	ZINC PLATED
5	GASKET	NEOPRENE	BLACK
4	RECEPTACLE SHELL	NYLON	BLACK
3	PIN CONTACT	BRASS ALLOY	UN-PLATED
2	MALE INSERT	RUBBER	YELLOW
1	WIRE,12AWG,1015/TEW	PVC	SEE WIRING DIAGRAM
ITEM	DESCRIPTION	MATERIAL	FINISH

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBER AS PER PCN#516685 EC NO: 830087 DRWN: PONNAM2025/07/24 CHK'D: GGA2025/08/05 APPR: GGA2025/08/05 INITIAL REVISION: DRWN: RSTONE2012/11/28 APPR: JFMURPHY2013/03/01			molex QUICK CHANGE RECEPTACLE #1/2-14" NPT 2-4 POLE, MALE, SINGLE KEY, #12 AWG								
INCH/MM		1.5:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)							PRODUCT CUSTOMER DRAWING			DOCUMENT NUMBER SD-130003-004			DOC TYPE PSD	DOC PART 001	REVISION A2
		MM	INCH												
4 PLACES		±	±												
3 PLACES		±	±												
2 PLACES		±	±												
1 PLACE		±	±												
0 PLACES		±	±												
ANGULAR TOL		±	°												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING C-SIZE	SERIES 130003	MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1			