





RoHS compliant
by exemption



3	2	Clinch nut	FT-4-40 / Steel	tin plated
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	black
<i>No.</i>	<i>St.</i>	<i>Part</i>	<i>Type Description/Material</i>	<i>Surface plating/Colour/Class</i>

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE		MEASUREMENTS WITHOUT TOLERANCE ACC. TO			molex			
	mm		2:1		ISO 2768-mK						
	 = 0					CURRENT REVISION			FCT D-Sub Mixed-Layout Connector		
 = 0											
 = 0											
					DRWN: DRAWN BY MTeubel 27-02-2020			PRODUCT CUSTOMER DRAWING			
					APPR: APPR BY MTeubel 27-02-2020						
	2		24130		INITIAL REVISION			MATERIAL NUMBER			
	1				DRWN: DRAWN BY sschref 05-03-2004			REVISION			
	REV.		CH.-NO.		APPR: APPR BY ffloßmann 05-03-2004			1731070156 2			
REPLACEMENT FOR:			FRIST ANGLE PROJECTION		DRAWING		DOCUMENT NUMBER			CUSTOMER	
					A3-SIZE		FT2W2PC-K120			GENERAL MARKET	
										SHEET NUMBER 1 OF 1	

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUBICATED NOR MADE AVAILABLE TO A THIRD PARTY,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.