



COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUBICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.


AWG
18-22




AWG
20-24





AWG
26-28



AWG 32



AWG
20-24



PIN


Material: Brass

SOCKET


Material: Copper alloy

SOCKET


Material: Copper alloy with
sleeve made of stainless steel





FK20SL




FK20SL26




FK20SL32



FK20S



FK20S26



Ordering Example FK20SL-08V-5783

Crimp socket contact for wire size AWG 20-24.
Plating 0.8µm Au over Ni,
Packing see packaging specification.

Availability on request, also nonmagnetic contacts.

Crimping Tools see catalogue.

Crimping Guideline see document: AM0650 (2195600650)

Packaging specification: 1731120004-PK

RoHS compliant
by exemption

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK			molex FCT Machined Contacts for Crimp Connectors					
	mm		5:1										
					CURRENT REVISION								
					DRWN: DRAWN BY mteubel 08-07-2025								
					APPR: APPR BY msteinbrueck 09-07-2025								
	14		24140		INITIAL REVISION			PRODUCT CUSTOMER DRAWING					
	13		24140										
	REV.		CH.-NO.		DRWN: DRAWN BY sschref 23-04-2015			MATERIAL NUMBER			REVISION		
				APPR: APPR BY jmairose 27-04-2015			see table			14			
REPLACEMENT FOR:			FIRST ANGLE PROJECTION		DRAWING			DOCUMENT NUMBER			CUSTOMER		SHEET NUMBER
					A3-SIZE			FK20-xx			GENERAL MARKET		1 OF 1