







ITEM	DESCRIPTION
1	SCREW
2	EXTERNAL THREAD COVER
3	INSERT
4	GASKET
5	GROMMET
6	EXTERNAL THREAD NUT

C28200NOR****

SERIES _____
C28= EXTERNAL THREAD FORM A
POLES _____
2= 2 POLE & 3= 3 POLE
THREAD _____
00 = EXTERNAL THREAD
MATERIAL AND HOUSING COLOR _____
G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK UL V0, T=TRANSPARENT
GROUND POSITION _____
0= UNMOUNTED, 2= H12, 3=H3, 6 =H6 & 9= H9
SCREW AND GASKET _____
R= INTEGRATED NBR GASKET AND IP67 SCREW
S= INTEGRATED SILICONE GASKET AND IP67 SCREW
T= PROFILE NBR GASKET AND IP67 SCREW
NON STANDARD PACKAGING _____
CN= BULK PACK UN-MOUNTED
SN= BULK PACK MOUNTED
67= NEUTRAL PACKAGING
CF= BULK PACK FULLY MOUNTED
ADDITIONAL CODES _____
SA= UL AGENCY APPROVED

NOTES:

1. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED
2. PRODUCT SPEC: SEE PS-121201-001
3. PACKAGING SPEC: SEE PK-121201-001
4. CABLE SIZES 4 - 9 mm DIAMETER
5. TIGHTENING TORQUE: SEE PS-121201-001
6. GROUND POSITION SHOWN H12

LAST INSPECTION NUMBER USED 8

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515767					molex							
	mm		1:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
	ANGULAR TOL		±		°		TYPE A ASSEMBLY SERIES 121201										
4 PLACES		±															
3 PLACES		±															
DIVISIONAL SYMBOLS	2 PLACES		±		0.1		PRODUCT CUSTOMER DRAWING										
	1 PLACE		±		0.2												
	0 PLACES		±														
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION			DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						A2-SIZE		121201		SD-121201-003		PSD		001		N3	
									SEE TABLE		GENERAL MARKET				SHEET NUMBER		
															1 OF 2		

molex

TYPE A ASSEMBLY
SERIES 121201

PRODUCT CUSTOMER DRAWING

SD-121201-003

PSD

001

N3

10	9	8	7	6	5	4	3	2	1	
F										F
E										E
	D									
C										
	B									
A										