

4

3



2

1


© 2019 TE Connectivity. All Rights Reserved.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	K	REVISED TO MATCH THE PART REVISION	06NOV2019	MK	CF
	K1	REVISION RECORD UPDATED	12NOV2019	MK	CF
	K2	REVISED PER PCN-22-153957	18AUG2022	SN	AW
	K3	REVISED PER PCN-23-165384	19JAN2023	MK	AW






OVAL SHAPE
AFTER DEMOLDING



3-D VIEW
CLOSED



3-D VIEW
OPEN



4 CIRCULAR DIMENSIONS CAN NOT BE MEASURED WITHOUT USING A GAGE OR AN ADEQUATE CONNECTOR DUE TO WARPAGE AFTER DEMOLDING.

3. MATERIAL: NYLON 66, COLOR: BLACK


2. SUITABLE WITH CORRUGATED TUBES SIZE NW 17, 19 AND 26.

1. THIS PART MATES WITH HDP24/26-24-XP/SX-L017.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCH[mm]



MATERIAL
VYDYNE 47H
PA 6/6

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025[0.63]
4 PLC ±
ANGLES ±0° 30' 0"

FINISH

-

-

DWN 20OCT2004

R. MESSENGER

CHK 30SEP2008

A. JAIME

APVD 01OCT2008

R. REED

PRODUCT SPEC

108-151015

APPLICATION SPEC

114-151015

WEIGHT

30 g

CUSTOMER DRAWING

TE INTERNAL PN

2428-010-2405

DEUTSCH PN

ZPF000000000146919



TE Connectivity

NAME
COVER STRAIGHT SIZE 24
HDP L017 MODS ONLY
TUBE SIZE NW 17, 19, 23 AND 26

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 4AFU8 C-2428-010-2405

SCALE

1:1

SHEET

OF

1

REV

K3