









REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P19720	4-21-08	ADD



- 8 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
7. PLUG IS RATED AT 150°C.
6. MATERIAL - HOUSING: PLASTIC, GROMMET: RUBBER.
5. THIS PLUG MATES WITH DTMH04-3P* AND DTM04-3P* RECEPTACLE.
(* = A,B,C,D KEYS)
- 4 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
- 3 TERMINAL POSITION ASSURANCE (TPA) LOCK PRE-MOUNTED: WMH-3S*.
(* = A,B,C,D KEYS)
2. ALL DIMENSIONS ARE $\pm .025$ [0.64].
1. ALL DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED






CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.5]

SIGNATURE & DATE	
DR	J. APOSTOL 07DEC2007
CHK	R. MIGA 4/16/08
PE	D. Whitaker 4/16/08
APPD	D. Meyer 4/16/08
SCALE	NONE

PLUG
3 PIN CONTACT
SIZE 20
COLOR: BLACK
DTMH SERIES
ENVELOPE

EP 180	MATL. CODE
DEUTSCH INDUSTRIAL	3850 INDUSTRIAL AVE. HEMET, CA 92545
B	DTMH06-3S*
DWG SIZE	CODE 11139 SHEET 1 OF 2


REV NC	DTMH06-3S*	REVISIONS			
		SYM	DESCRIPTION	DATE	APPROVED
		NC	SEE SHEET 1	4-21-08	RLP



KEYWAY

DTMH06-3A


-A- KEY
TPA COLOR: GREY



KEYWAY

DTMH06-3B


-B- KEY
TPA COLOR: BLACK



KEYWAY

DTMH06-3C

-C- KEY
TPA COLOR: GREEN



KEYWAY

DTMH06-3D

-D- KEY
TPA COLOR: BROWN

NOTES:

SIGNATURE & DATE		PLUG 3 PIN CONTACT SIZE 20 COLOR: BLACK DTMH SERIES ENVELOPE	EP 180		MATL. CODE
DR	J. APOSTOL 07DEC2007				3850 INDUSTRIAL AVE. HEMET, CA 92545
CHK	<i>[Signature]</i> 4/16/08				
PE	<i>[Signature]</i> 2/27/08		B		DTMH06-3S*
APPD	<i>[Signature]</i> 2/26/08				
SCALE NONE			DWG SIZE	CODE 11139	SHEET 2 OF 2