









8. SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
7. PART MODIFICATION: RECEPTACLE IS RATE AT 150°C (COLOR: BLACK).
6. MATERIAL - HOUSING/RETAINER: PLASTIC; GROMMET: RUBBER.
5. CONNECTOR DESIGNED TO BE USED WITH DTM06-12S*-**** PLUGS.
(*) = A,B,C,D KEYS, (****) = ALL HIGH TEMPERATURE MODIFICATIONS.
CONSULT FACTORY FOR MODIFICATIONS.
4. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
3. SECONDARY WEDGE LOCK SOLD SEPARATELY: WM-12P.
2. DIMENSION TOLERANCE: $\pm .025$ [.64].
1. DIMENSIONS ARE IN INCHES [mm].
- NOTES: UNLESS OTHERWISE SPECIFIED

REV
A DTM04-12P*-EE04

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI9500	8/22/07	R.D.R.
A	REVISED PER E.O. PI9776	4-7-08	RDR

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.5]

SIGNATURE & DATE	
DR	D. MEYER 04/27/07
CHK	7/6/07/08
PE	4/7/08
APPD	4/7/08
SCALE	NONE

RECEPTACLE
12 CONTACTS, SIZE 20
A,B,C,D KEYS
-EE04 MOD
DTM SERIES

ENVELOPE

EP 172	MATL. CODE
 3850 INDUSTRIAL AVE. HEMET, CA 92545	
B DTM04-12P*-EE04	
DWG SIZE	CODE 11139 SHEET 1 OF 2

REV	DTM04-12P*-EE04	REVISIONS			
A		SYM	DESCRIPTION	DATE	APPROVED
		A	SEE SHEET 1	4-7-08	ADR

DTM04-12PA-EE04
KEY -A-
COLOR: BLACK

DTM04-12PB-EE04
KEY -B-
COLOR: BLACK

DTM04-12PC-EE04
KEY -C-
COLOR: BLACK

DTM04-12PD-EE04
KEY -D-
COLOR: BLACK

NOTES:

SIGNATURE & DATE		RECEPTACLE 12 CONTACTS, SIZE 20 A,B,C,D KEYS -EE04 MOD DTM SERIES ENVELOPE	EP 172	MATL. CODE
DR	D. MEYER 04/27/07		3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	<i>[Signature]</i> 4/10/08		DEUTSCH INDUSTRIAL	
PE	<i>[Signature]</i> 4/13/08		B DTM04-12P*-EE04	
APPD	<i>[Signature]</i> 4/16/08		DWG SIZE	CODE 11139
SCALE	NONE			SHEET 2 OF 2