

BUD	PART NAME	NEMA 4X PLASTIC BOX	PART No.	PN-1347, PN-1347-C, PN-1347-DG	REVISION DATE	12/8/25


NOTES:


1. MATERIAL AND FINISH:
   POLYCARBONATE UL94-HB, UV STABILIZED, SERVICE TEMPERATURE RANCE: -40˚C TO 120˚C, LIGHT GRAY BODY & COVER
   -C - SAME AS EXCEPT CLEAR COVER.
   ABS (DARK GRAY) SERVICE TEMPERATURE RANCE: -40˚C TO +80˚C
2. DESIGNED MEETS IP65 OF IEC 529.
3. UL LISTED (E194432) NEMA 1, 2, 4, 4X, 12, AND 13
4. GASKET (PRE-INSTALLED) SILICON SPONGE STRIP GASKET




DETAIL B









DETAIL D




BODY



SECTION A-A



COVER



SECTION C-C

DRAWING FOR REFERENCE
WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSE.