



Note: edges not dimension R0.25

Scale	2 : 1			
THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS				
©				
DR	C	29Nov06	Modificati valori di planarità e perpendicolarità (vedi dettaglio C)	SB
	B	24Nov06	Indicate superfici a vista	SB
	A	16Nov06	ORIGINAL (was DEV BS595-2)	MG

AAVID THERMALLOY
EUROPE www.aavidthermalloy.com

Via XXV Aprile, 32
40057 Cadriano - Bologna ITALY
Tel. +39 051 764011
Fax +39 051 764090

Cheney Manor
SWINDON WILTS SN2 2QN UK
Tel. +44 1793 401400
Fax +44 1793 615396

COMPANY WITH QUALITY SYSTEM CERTIFIED BY LRQA ISO 9001:2000

Format	A4	REV	Date	Revision description	By
Die n.	MATERIAL Aluminium EN AW-6060 T5 or T6			DRAWING n.	BS595
Factor	GENERAL TOLERANCES UNI EN 12020/2			Vis. n.	411151
Perim.	445 mm			Drawn	L. Caporale
Area	566 mm ²	FINISH UNFINISHED		Check	
Weight	1.528 kg/m	Description: RAW PROFILE-AL-411151 BS595-CUSTOM-5100			