





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	A DIA.	MT'G RIVET	MT'G SCREW	FOR USE WITH THE FOLLOWING PANDUIT CABLE TIES	WEIGHT lbs/100 pcs (g)/100 pcs
LHMS-S5-	0.125 0.135	1/8	#5	M = MINATURE I = INTERMEDIATE S = STANDARD	0.56 (254.24)
LHMS-S6-	0.140 0.150	9/64	#6		0.56 (254.24)
LHMS-S10-	0.190 0.195	3/16	#10		0.54 (245.16)

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. CAN SUBSTITUTE #5 SCREW FOR A #6 SELF THREADING SCREW.
3. CAN SUBSTITUTE #6 SCREW FOR A #8 SELF THREADING SCREW.



DIMENSIONS IN BRACKETS ARE METRIC [mm]

END FILM/LAYERS G00239BT_PB_LHMS_02

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

LHMS
LIGHTENING HOLE MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (1.00X) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

2	6/26/01	LGG	CHG DIM ON 'A' FOR LHMS-S5 WAS .125/.130. ADD REF & CHG DIM FROM 1.100 TO 1.084.	GB0239BT					
1	6/26/01	LGG	UPDATED FOR WEB	GB0239BT	1				
R	5/03/95	CBJ	INITIAL RELEASE	GB0239BT	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		

DRAWN BY CBJ

DATE 5/03/95

CHK'D

MAT'L:

NYLON 6/6

SCALE 1 : 1

DRAWING NO.

GB0239BT

DWG

A
SIZE