



- 1.CABLE:NO UL.,2BAWG(7/0.127),TINNED AND STRANDED COPPER WIRE
INSULATOR:PVC,ID:0.85mm ,CABLING:50C+DRAIN WIRE
SHIELD:AL/MY COVERAGE
JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE
- 2.2PCS CONNECTOR:CENTRONIC 50 WAYS MALE SOLDER TYPE CONNECTOR
INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE
CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED
SHELL:NICKEL PLATED.
CONNECTOR COMPLIANCE ROHS
- 3.HOOD:PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER
MOLD AND INJECTION OUTER MOLD
COLOR:BEIGE,COMPLIANCE ROHS
- 4.Fulfill ROHS Guideline
- 5.ELECTRONIC TEST: 100% OPEN SHORT+MISS WIRE TEST

PIN OUT

C50PIN PLUG(P1)	WIRE	C50PIN PLUG(P2)
1	_____	1
2	_____	2
3	_____	3
4	_____	4
5	_____	5
6	_____	6
7	_____	7
8	_____	8
9	_____	9
10	_____	10
11	_____	11
12	_____	12
13	_____	13
14	_____	14
15	_____	15
16	_____	16
17	_____	17
18	_____	18
19	_____	19
20	_____	20
21	_____	21
22	_____	22
23	_____	23
24	_____	24
25	_____	25
26	_____	26
27	_____	27
28	_____	28
29	_____	29
30	_____	30
31	_____	31
32	_____	32
33	_____	33
34	_____	34
35	_____	35
36	_____	36
37	_____	37
38	_____	38
39	_____	39
40	_____	40
41	_____	41
42	_____	42
43	_____	43
44	_____	44
45	_____	45
46	_____	46
47	_____	47
48	_____	48
49	_____	49
50	_____	50
SHELL	DRAIN WIRE	SHELL

PART NO	SHEET NO	1	THIRD ANGLE PROJECTION		
TITLE: C50 PIN MALE TO C50 PIN MALE BEIGE COLOR			SCALE	N.T.S	DRAWN BY & DATE
			SIZE	A4	CHECKED BY & DATE
DWN NO			UNIT		APPROVED BY & DATE
			<input checked="" type="checkbox"/> MM	<input type="checkbox"/> INCH	