



No.	DESCRIPTION	Q'TY	Supplier
5	UL1007 24AWG, JACKET RED, BLACK		M541
4	UL2651 40C 28AWG, FLAT CABLE, PITCH 1.27mm, GREY		M2
3	5 1/4" MALE	1	M31
2	M044 PIN CONNECTOR, BLACK	1	M385
1	IDC SOCKET 40 PIN CONNECTOR, BLACK	1	M47

APPROVED				Cable Length Tolerances: 0 ~0.2M ±0.01M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
CHECKED				
DRAWING	???	ITEM NO.	RB-377	