



DIN-Standard Insertion Socket Outlet with Protective Cap

Dust Proof and Splash Proof version. With 6.3 mm flat terminals. Fastening by hexagon nut, fitting for Standard and Universal Plug, 16 A/12-24 V max., TÜV certified and monitored to DIN ISO 4165. Opening for insertion: 18 mm.

DIN-Standard Insertion Socked Outlet with Protective CapBP

SP

PU = 500

PU = 20

16 A

57607002

57607003

